



Implantable Multi-pin Feedthrus

PA&E's ceramic sealing technology is the solution of choice for producing headers with large pin counts. Our design flexibility allows designers to group families of pins where they need them, in headers that fit their design. Our technology can usually be adapted to space available.

Flexibility ■ Many options for pin arrangements

Innovative ■ Pt/Lr pins sealed into titanium with ceramic

Hermetic ■ Leak rate < 10^{-9} atm-cm³/s



Implantable Hermetic Connectors

Design History

We have been making implantable devices in volume for over 30 years.

Design Flexibility

Complex shapes can be easily realized without the need for elaborate and expensive mold tooling. Our expertise in titanium machining enables us to effectively produce a wide variety of geometries.

Development Flexibility

Need to move a pin? A simple engineering change and programming change and the next version is ready. No complex mold tools to scrap.

Better Standoff Distances

Our pins are sealed into headers using our Kryoflex[®] ceramic sealant - an excellent insulator. Other technologies such as gold braze use a metallic braze filler as a sealant, which, for a given geometry, reduces the effective electrical pin-to-body standoff distance.

Transparency: Prototypes to Production

Our prototype parts are identical to the final production parts. Need 50 parts to start your qualification process? No problem. You can start qualification testing with these parts with assurances that future parts will be identical. Other technologies use different production strategies depending on volume, so testing performed on low volume samples may have to be redone for larger volume production parts produced with different methods.



For further information contact us at sales@pacaero.com or visit our web site www.pacaero.com