



Implantable Package Assemblies

PA&E's technology is especially suited to situations where there may not be space available to weld in a separate header. Compact packages with integrated feedthru pins provide designers with elegant one-piece design possibilities. That means fewer piece parts, fewer critical welds and fewer points of potential failure.

RF Transparency ■ Signals into/out of implanted devices

Innovative ■ Composite titanium and zirconia

Hermetic ■ Leak rate < 10^{-9} atm-cm³/s



Implantable Electronic Packaging

Design History

We have been making implantable devices in volume for over 30 years.

Design Flexibility

Complex shapes can be easily realized without the need for elaborate and expensive mold tooling. Our expertise in titanium machining enables us to effectively produce a wide variety of geometries.

Development Flexibility

Need to move a pin? A simple engineering change and programming change and the next version is ready. No complex mold tools to scrap.

Better Standoff Distances

Our pins are sealed into headers using our Kryoflex[®] ceramic sealant - an excellent insulator. Other technologies such as gold braze use a metallic braze filler as a sealant, which, for a given geometry, reduces the effective electrical pin-to-body standoff distance.

Transparency: Prototypes to Production

Our prototype parts are identical to the final production parts. Need 50 parts to start your qualification process? No problem. You can start qualification testing with these parts with assurances that future parts will be identical. Other technologies use different production strategies depending on volume, so testing performed on low volume samples may have to be redone for larger volume production parts produced with different methods.

For further information contact us at sales@pacaero.com or visit our web site www.pacaero.com

